

PACIFIC MAGNETIC LIFTER

Model	Capacity	Suitable Thickness of plate (mm)	Material of Plate	Carbon Content	Absorbability (kg)
PML-1	100	>25	≤45# steel	Low	=100
PML-3	300	>35	≤45# steel	Low	=300
PML-6	600	>40	≤45# steel	Low	=600
PML-10	1000	>50	≤45# steel	Low	=1000
PML-20	2000	>60	≤45# steel	Low	=2000

Note: Use of plate with high-carbon content will reduce the absorbability to less than 50% of rated capacity. Use of plate with high carbon content not recommended.

